

### Overview



The clamp-on SITRANS FUG1010 Gas check metering kit is an all-inclusive solution developed especially for verifying the accuracy and performance of any brand or type of flowmeter. The kit is ideal for natural and process gas applications, including check metering, allocation, production, storage and gas fired power station applications. The flowmeter is available with FM/CSA or ATEX approval.

### Benefits

- Performance check or verification of any type or brand of flow meter
- WideBeam technology provides improved accuracy over a wide range of flow velocity and operating pressure
- Tolerant of most wet gas conditions
- Immune to most pressure reducing valve noise
- Fast, easy and cost-efficient on-site measurement of any convoluted pipe from 50 ... 1200 mm (2 ... 48") up to 15.7 mm (0.62") pipe wall thickness
- Delivered as an all inclusive kit in a sturdy rolling case that holds all the equipment needed to conduct performance and verification tests (cables, multiple sensors, transmitter, etc.)

### Application

The SITRANS FUG1010 Gas check metering kit is ideal for most natural and process gas industry applications, including:

- Check metering
- Allocation
- Lost and unaccounted for (LAUF) gas analysis
- Production
- Storage

### Design

- IP65 (NEMA 4X) wall mount enclosure constructed of fiber-glass reinforced polyester with stainless steel hardware and polyester keypad
- Dual channel

### Function

- Integral 33 button keypad and large (128 x 240 pixel) graphic display visible up to 12 m (40 ft) away
- Current, voltage, frequency and RS 232 outputs (see Technical specification section for details)
- Analog inputs for pressure and temperature
- Internal AGA-8 table for fixed gas composition is available for standard volume computation
- Upward compatibility and compliance with AGA-10 speed of sound measurement practice
- Bi-directional flow operation
- English, Spanish, German, Italian and French language options

### Technical specifications

Pipe sizes	50 ... 1200 mm (2 ... 48") up to 15.7 mm (0.62") pipe wall thickness
Accuracy	±0.5 %...1.0 % of flow rate
Flow range	30 m/s (100 ft/s) bidirectional
Media temperature	-40 ...+60 °C (-40 ... +140 °F)
Enclosure ratings	IP65 (NEMA 4X)

See page 3/389 for complete technical specifications

### Certificates and approvals

FM and CSA

- Transmitter  
N-I Class I, Div 2  
S Class II, Div 2
- Sensor  
I.S. Class I, II, Div 1

ATEX

- Transmitter:  
Ex II (1) G [Ex ia] IIC  
Ex II 3 (1) G Ex nC [ia] IIC T5

CE

- Sensors:  
Ex II 1 G Ex ia IIC T5  
EMC Directive 2014/30/EU  
ATEX Directive 2014/34/EU

### Selection and Ordering data

Article No.

#### SITRANS FUG1010 Gas Check Metering Kit

- FM/CSA approved
- ATEX approved

**CQO:FUG-GASKIT**  
**CQO:FUG-GASAKIT**

#### Content of delivery

1	Dual channel dedicated transmitter (FM/CSA or ATEX approved)
1 pair	Transportable sensors C1 <sup>1)</sup> Pipe: od 3.500 inch, wt 0.216 inch, carbon steel
1 pair	Transportable sensors C2 <sup>1)</sup> Pipe: od 6.625 inch, wt 0.280 inch, carbon steel
1 pair	Transportable sensors D1 <sup>1)</sup> Pipe: od 10.750 inch, wt 0.365 inch, carbon steel
1 pair	Transportable sensors D2 <sup>1)</sup> Pipe: od 16.000 inch, wt 0.500 , carbon steel
2 pairs	Sensor cables 6m (20 ft)
2 pairs	Mounting frames
2	Spacer bar (dedicated)
1	Mounting strap
4	Couplant CC128
1 kit	Couplant/Damping Film
1	Flow case
1	Flowmeter manual
1	Laminated card set

<sup>1)</sup> Made with stainless steel construction.